

The Pulsatron Series MP is a true microprocessor controlled instrument for precise and accurate metering control. Packed with standard features, the Series MP include automatic control via 4-20mA or 20-4 mA inputs, external pace with stop feature and 16 character LCD display with support for English, French, and German languages.

Nineteen distinct models are available, having pressure capabilities to 300 PSIG (21 BAR) @ 3 GPD (0.5 lph), and flow capacities to 504 GPD (79.5 lph) @ 20 PSIG (13 BAR), with a turndown ratio of 1000:1. Metering performance is reproducible to within  $\pm 2\%$  of maximum capacity.

## Features

- Automatic Control, Fully scalable 4-20mA current signal.
- Flow Verification on select sizes.
- Flow Totalization.
- Relay Output for computer interface or AC power.
- Simple Prompts in plain language.
- Available in four languages, English, French, German, and Spanish.
- Alarm Signals for signal loss, full count, circuit failure, pulse overflow and pulse rate high.
- Liquid low-level indicator capability is standard.
- Timed Sequences can be set for selected intervals and rate for repetitive metering.
- Pulse Signals can be multiplied or divided by 1 to 999.
- Flow Rate is displayed as GPH, GPD, or LPH.
- Large easy to read backlit LCD display.

## Controls



### Manual Stroke Rate

- Turn-Down Ratio 100:1

### Stroke Length

- Turn-Down Ratio 10:1

### 4-20mA or 20-4mA Input

- Automatic Control
- Fully Scalable
- Turn-Down Ratio 100:1



### Flow Verification

- Monitors pump output to protect against loss of flow.
- Visual Notification.

## Operating Benefits

- Reliable metering performance.
- Rated "hot" for continuous duty.
- High viscosity capability.
- Leak-free, sealless, liquid end.



## Aftermarket

- KOPkits
- Gauges
- Dampeners
- Pressure Relief Valves
- Tanks
- Pre-Engineered Systems
- Process Controllers (PULSAblue, MicroVision)



# PULSAtron® Series MP

## Specifications and Model Selection

MODEL		LMK2	LMB2	LMA2	LM D3	LMB3	LMA3	LMK3	LMF4	LM D4	LMB4	LMH4	LMG4	LME4	LMK5	LMH5	LMH6	LMK7	LMH7	LMH8
Capacity nominal (max)	GPH	0.13	0.21	0.25	0.50	0.50	0.50	0.60	0.85	0.90	100	170	175	185	250	3.15	5.00	8.00	10.00	2100
	GPD	3	5	6	12	12	12	14	20	22	24	41	42	44	60	76	120	192	240	504
	LPH	0.5	0.8	0.9	19	19	19	2.3	3.2	3.4	3.8	6.4	6.6	7.0	9.5	119	18.9	30.3	37.9	79.5
Pressure (max)	PSIG	300	250	150	250	150	100	100	250	150	100	250	150	100	150	150	100	50	35	20
	BAR	21	17	10	17	10	7	7	17	10	7	17	10	7	10	10	7	3.3	2.4	13
Connectio	Tubing	1/4" ID X 3/8" OD 3/8" ID X 1/2" OD												3/8" ID X 1/2" OD 1/2" ID X 3/4" OD (LPH8 ONLY) FLOWVERIFICATION (See Note)						
	Piping	1/4" FNPT												1/4" FNPT 1/2" FNPT						

Note: Flow Verification: Available on K3, B4 and E4 with connection code t; H6, K7 and H7 with connection code H; 1/4" ID x 3/8" OD only.

### Engineering Data

Pump Head Materials Available:	GFPPL PVC PVDF 316 SS PTFE-faced CSPE-backed
Diaphragm:	PTFE
Check Valves Materials Available:	PTFE CSPE Viton
Seats/O-Rings:	Ceramic
Balls:	PTFE 316 SS Alloy C
Fittings Materials Available:	GFPPL PVC PVDF
Bleed Valve:	Same as fitting and check valve selected, except 316SS
Injection Valve & Foot Valve Assy:	Same as fitting and check valve selected
Tubing:	Clear PVC White PE

Important: Material Code - GFPPL=Glass-filled Polypropylene, PVC=Polyvinyl Chloride, PE=Polyethylene, PVDF=Polyvinylidene Fluoride, CSPE=Generic formulation of Hypalon, a registered trademark of E.I. DuPont Company. Viton is a registered trademark of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

### Custom Engineered Designs Pre-Engineered Systems

Pulsafeeder's Pre-Engineered Systems are designed to provide complete chemical feed solutions for all electronic metering applications. From stand alone simplex pH control applications to full-featured, redundant sodium hypochlorite disinfection metering, these rugged fabricated assemblies offer turn-key simplicity and industrial-grade durability. The UV-stabilized, high-grade HDPE frame offers maximum chemical compatibility and structural rigidity. Each system is factory assembled and hydrostatically tested prior to shipment.


### Dimensions

Series MP Dimensions (inches)																	
Model No.	A	B	B1	C	C1	D	E	Shpg Wt	Model No.	A	B	B1	C	C1	D	E	Shpg Wt
LMA2	5.4	10.3	-	10.8	-	7.5	8.9	13	LMH4	6.2	10.9	-	11.2	-	8.2	9.5	21
LMA3	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH5	6.2	11.3	-	11.2	-	8.2	9.9	21
LMB2	5.4	10.3	-	10.8	-	7.5	8.9	13	LMH6	6.2	11.3	-	11.2	-	8.2	9.9	21
LMB3	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH7	6.1	11.7	-	11.2	-	8.2	10.3	21
LMB4	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH8*	6.1	-	10.9	-	10.6	8.2	-	25
LM D3	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK2	5.4	10.3	-	10.8	-	7.5	8.9	13
LM D4	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK3	5.4	10.6	-	10.7	-	7.5	9.2	13
LME4	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK5	5.4	10.9	-	11.7	-	7.5	9.5	18
LMF4	5.4	10.6	-	11.7	-	7.5	9.2	18	LMK7	6.1	11.7	-	11.2	-	8.2	10.3	21
LMG4	5.4	10.6	-	11.7	-	7.5	9.2	18									

NOTE: Inches X 2.54 = cm / \* the LMH8 is designed without a bleed valve available

### Engineering Data

Reproducibility:	+/- 2% at maximum capacity
Viscosity Max CPS:	For viscosity up to 3000 CPS, select connection size 3, 4, B or C with 316SS ball material. Flow rate will determine connection/ball size. Greater than 3000 CPS require spring loaded ball checks. See Selection Guide for proper connection.
Controls:	6-Station Membrane Switch
Status Display:	16-Position LCD Dot Matrix Backlight
LED Indicator Lights, Panel Mount:	Power On - Green Pulsing - Green Flashing Stop - Red
Stroke Frequency Max SPM:	125
External Stroke Frequency Control (Automatic):	4-20 mADC, 20-4 mADC External Pacing
Output Relay (Signal Level Option):	24 VDC, 10 mA
Output Relay (Power Option):	250 VAC, 50/60 HZ, 0.5A
Stroke Frequency Turn-Down Ratio:	100:1
Stroke Length Turn-Down Ratio:	10:1
Power Input:	115 VAC/50-60 HZ/1 ph 230 VAC/50-60 HZ/1 ph
Average Current Draw:	
@ 115 VAC; Amps:	1.0 Amps
@ 230 VAC; Amps:	0.5 Amps
Peak Input Power:	300 Watts
Average Input Power @ Max SPM:	130 Watts



pulsafeeder.com



27101 Airport Rd  
Punta Gorda, FL 33982  
Phone: ++1(941) 575-3800  
Fax: ++1(941) 575-4085

An ISO 9001 and ISO 14001 Certified Company



EMP027 H10